

| 长度 Length (mm) 容量 Capacity (mm) | | 软管规格与容量参考表 Reference Table for Specification and Capacity of Cosmetic Plastic Tube | | | | | | | | | | | | | | | |
|--|-----------|---|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| | | Ø13 | Ø16 | Ø19 | Ø22 | Ø25 | Ø28 | Ø30 | Ø33 | Ø35 | Ø38 | Ø40 | Ø45 | Ø50 | Ø55 | Ø60 | |
| ml | oz | | | | | | | | | | | | | | | | |
| 3 | 0.10 | 45 | | | | | | | | | | | | | | | |
| 5 | 0.18 | 61 | 50 | | | | | | | | | | | | | | |
| 8 | 0.27 | | 70 | | | | | | | | | | | | | | |
| 10 | 0.34 | | 78 | 66 | | | | | | | | | | | | | |
| 12 | 0.40 | | 85 | 72 | | | | | | | | | | | | | |
| 15 | 0.50 | | 100 | 85 | 60 | | | | | | | | | | | | |
| 20 | 0.70 | | | 100 | 85 | 60 | 55 | | | | | | | | | | |
| 25 | 0.90 | | | 110 | 100 | 78 | 70 | | | | | | | | | | |
| 30 | 1.00 | | | | 110 | 90 | 80 | 75 | 65 | | | | | | | | |
| 35 | 1.20 | | | | 130 | 103 | 90 | 82 | 77 | 75 | | | | | | | |
| 40 | 1.40 | | | | | 115 | 98 | 90 | 86 | 81 | | | | | | | |
| 45 | 1.50 | | | | | 126 | 110 | 100 | 92 | 87 | | | | | | | |
| 50 | 1.70 | | | | | 137 | 120 | 108 | 98 | 91 | | | | | | | |
| 55 | 1.90 | | | | | | 125 | 115 | 105 | 96 | 84 | | | | | | |
| 60 | 2.00 | | | | | | 138 | 122 | 112 | 102 | 90 | | | | | | |
| 65 | 2.20 | | | | | | | 129 | 118 | 107 | 95 | 90 | | | | | |
| 70 | 2.40 | | | | | | | 136 | 124 | 113 | 100 | 94 | | | | | |
| 75 | 2.50 | | | | | | | 143 | 132 | 119 | 105 | 97 | | | | | |
| 80 | 2.70 | | | | | | | 150 | 137 | 124 | 110 | 101 | | | | | |
| 85 | 2.90 | | | | | | | | 142 | 130 | 115 | 106 | | | | | |
| 90 | 3.00 | | | | | | | | 145 | 135 | 120 | 111 | | | | | |
| 95 | 3.20 | | | | | | | | | 141 | 125 | 116 | 92 | | | | |
| 100 | 3.40 | | | | | | | | | 148 | 130 | 119 | 95 | | | | |
| 110 | 3.70 | | | | | | | | | 162 | 145 | 128 | 102 | | | | |
| 120 | 4.10 | | | | | | | | | | 155 | 137 | 113 | 100 | | | |
| 130 | 4.40 | | | | | | | | | | 164 | 145 | 123 | 110 | | | |
| 140 | 4.70 | | | | | | | | | | 173 | 154 | 132 | 118 | | | |
| 150 | 5.10 | | | | | | | | | | 181 | 162 | 140 | 124 | | | |
| 160 | 5.40 | | | | | | | | | | | 170 | 150 | 130 | | | |
| 170 | 5.80 | | | | | | | | | | | 178 | 158 | 137 | | | |
| 180 | 6.10 | | | | | | | | | | | 186 | 164 | 143 | 124 | | |
| 190 | 6.40 | | | | | | | | | | | | 170 | 149 | 128 | | |
| 200 | 6.80 | | | | | | | | | | | | 176 | 156 | 134 | | |
| 210 | 7.10 | | | | | | | | | | | | | 180 | 164 | 140 | 120 |
| 220 | 7.40 | | | | | | | | | | | | | 185 | 170 | 145 | 125 |
| 230 | 7.80 | | | | | | | | | | | | | | 175 | 150 | 130 |
| 240 | 8.10 | | | | | | | | | | | | | | 180 | 155 | 135 |
| 250 | 8.50 | | | | | | | | | | | | | | 185 | 160 | 140 |
| 260 | 8.80 | | | | | | | | | | | | | | 190 | | 145 |
| 270 | 9.10 | | | | | | | | | | | | | | 195 | | 150 |
| 280 | 9.50 | | | | | | | | | | | | | | 200 | | 153 |
| 290 | 9.80 | | | | | | | | | | | | | | 205 | | 157 |
| 300 | 10.2 | | | | | | | | | | | | | | 210 | | 161 |
| 320 | 10.8 | | | | | | | | | | | | | | | | 170 |
| 340 | 11.5 | | | | | | | | | | | | | | | | 178 |
| 360 | 12.2 | | | | | | | | | | | | | | | | 186 |
| 380 | 12.9 | | | | | | | | | | | | | | | | 190 |
| 400 | 13.5 | | | | | | | | | | | | | | | | 195 |

(1) 软管直径固定，长度可酌量伸减。

Tube diameter is set, length can be adjusted.

(2) 以上容量表仅做参考，可以根据客户需求在一定范围内调整。

Specifications are for reference only, and customer sizes are available.

(3) 上表所列管长是封尾后测量的结果，如客户自行封尾，管长需增加10-20mm。

Above tube length are the testing result after the sealing, if customer seals the tubes by himself, the tube length should increase 5-10mm.